

Bluetooth Pressure Sensor BluePSI User Guide

/ Important Notes

- Don't Install Battery when not in operation.
- Sensitive diaphragm inside. Do **NOT** stick anything into the pressure port.

Description

- 1) Battery Cap twist cap on top to open and install coin battery
- 2 Pressure Port connects to measurement port
- 3 Device Label-- lists device ID and pressure range

Electronic components and transmitter are contained within this top section.

⚠ Do *NOT* twist the upper section of the unit.

Use this portion to twist the unit when installing or uninstalling.



Included in the box


- Bluetooth Pressure Sensor (BluePSI) 1X
- User Guide 1X
- Coin Battery 1X
- Battery Spacer (for CR2032) 1X

Compatible Software

- iOS: MultiGage Reader
- Android: MultiGage Reader
- Windows: MultiGage Reader (BLE Dongle Required)
- The iOS app can be directly downloaded from the App Store for FREE.
- The Android app can be directly downloaded from the Google Play Store for FREE.
- Windows software is available on the Motionics website.

Ouick Start

- For first time use, follow instructions to install the battery.
- Plug in USB Bluetooth dongle if using Windows PC.
- Run one of the aforementioned Apps/software.
- In the main page, tap Scan/+ button to bring up a new pairing page.
- Wait for the software to finish scanning nearby devices, select BluePSIXXXX to connect.
 Device ID can be found on the BluePSI label.
- It might take multiple refreshes to find the device.
- Connection may take a few seconds.
 Once paired, instrument reading shows in the software.



- SENSOR BODY

Battery Installation (CR2050)

Specifications

- Measurement Range: Located on sensor label
- Accuracy: ±0.25%FS
- Proof Pressure: 2X measurement range
- Burst Pressure: 5X measurement range
- Bluetooth Low Energy Wireless Connection
- Wireless Data Transmission Interval: 5s (adjustable)
- Wireless Data Transmission Range: up to 20m
- Weather Proof: IP67
- Working Temperature: -4 to 185°F / -20 to 85°C
- Battery: CR2050/CR2032
- Pressure Port: ¼-18 NPT

Motionics, LLC www.motionics.com 8500 Shoal Creek Blvd Building 4 Suite 209, Austin, TX, 78757 © 2021 Motionics, LLC. All rights reserved. info@motionics.com

Made in the U.S.A.